


# OBO variable insulating traverse

## Simple. Safe. Fast as lightning

Optimised fastening  
fast and convenient



TBS Transient voltage and lightning protection systems





**OBO**  
BETTERMANN

# Fast, convenient installation

OBO adjustable insulating traverses permit quick and professional mounting of all standard 16 mm interception rods.

- Adjustable distance range of 550–1,000 mm
- Optimised fastening without drilling, even to stainless steel chimneys



Ordering data			
	Type	Design	Art. no.
	ISAV 1000 W	Wall mounting with 10 x 4.2 mm fastening holes with 4 x 6.9 mm fastening holes	5408 85 2
	ISAV 1000 R	Tube mounting Incl. tightening strap (2 m) and tension jack	5408 84 9

© OBO BETTERMANN Art. no. 9133356 04/2006 GB

OBO. Used by professionals



**OBO BETTERMANN GmbH & Co. KG**  
 P.O. Box 1120 · 58694 Menden, Germany  
 Phone +49 (0)23 73/89-0  
 Fax +49 (0)23 73/89-238  
 E-mail info@obo.de  
 www.obo-bettermann.com

**Central Technical Hotline**  
 Phone +49 (0)23 73/89-1500  
 Fax +49 (0) 23 73/89-1550  
 E-mail hotline@obo.de

