


OBO variable insulating traverse

Simple. Safe. Fast as lightning

Optimised fastening
fast and convenient



TBS Transient voltage and lightning protection systems





OBO
BETTERMANN

Fast, convenient installation

OBO adjustable insulating traverses permit quick and professional mounting of all standard 16 mm interception rods.

- Adjustable distance range of 550–1,000 mm
- Optimised fastening without drilling, even to stainless steel chimneys



Ordering data			
	Type	Design	Art. no.
	ISAV 1000 W	Wall mounting with 10 x 4.2 mm fastening holes with 4 x 6.9 mm fastening holes	5408 85 2
	ISAV 1000 R	Tube mounting Incl. tightening strap (2 m) and tension jack	5408 84 9

© OBO BETTERMANN Art. no. 9133356 04/2006 GB

OBO. Used by professionals



OBO BETTERMANN GmbH & Co. KG
 P.O. Box 1120 · 58694 Menden, Germany
 Phone +49 (0)23 73/89-0
 Fax +49 (0)23 73/89-238
 E-mail info@obo.de
 www.obo-bettermann.com

Central Technical Hotline
 Phone +49 (0)23 73/89-1500
 Fax +49 (0) 23 73/89-1550
 E-mail hotline@obo.de

