


# Another big hit:

The OBO pressure clip



## Lasso equals speed

The quicker, the better – this also applies to the installation of intermediate ceilings and partition walls. That is why we have not only changed the design of our pressure clip but also its function. As before, assembly is very simple using the M6 knock-in fixing. A new feature is the striking surface on the top, which guarantees high striking accuracy in the screw. After assembly the cables are passed under the clips in a “lasso technique” hand movement – and that’s all there is to it.



### Everything good comes from above: a striking surface on the top

It couldn't be easier: the knock-in fixing can be knocked in very conveniently and safely with a hammer.



### Structural reform: modified corrugated structure

The new corrugated structure not only looks good, it also creates a secure holder for all cable diameters.



### Keeping distance: spacer

For fixing larger cable diameters the OBO spacer is still available.

Pressure clip Type	For max. cables NYM 3 x 1.5 mm <sup>2</sup>	Pack qty	Order No. PA
2032	8	50	2205 01 7
2033	16	25	2205 03 3
2034	10	50	2205 04 1
2032/SP	8	100	2204 97 5
2033/SP	16	100	2204 98 3
2034/SP	10	100	2204 99 1

SP = big pack, polyamide light grey RAL 7035, halogen-free, for other versions (e.g. flame-retardant) see our VBS catalogue

Spacer Type	Colour	Pack qty	Order No. PS
2033/D	light grey	100	2205 09 2

Knock-in fixing Type	Size x plug length	Pack qty	Order No. PA
910/SD	6 x 40 mm	100	2351 06 4

## OBO. Used by professionals.



VBS TBS KTS BSS LFS UFS