


Pipe systems from OBO

Metal pipes with and without thread

Dimensions of M16-M63
including accessories

VBS Connection and fastening systems









OBO
BETTERMANN

Stapa armoured steel pipes for high mechanical requirements

As a solid complement to the legendary plastic Quick-Pipe system, OBO can now offer metal electrical installation pipes. These have either electrogal-

vanised or hot-dip galvanised surfaces and come with or without thread ends.

Both pipe versions can either be connected and extended using push-in or screw-in sleeves, and 90 degree pipe bends also allow user-friendly use.

	With thread			Without thread					
	Type/size	FT	G	Type/size	FT	G			
Pipe		SM16	2047 33 6	2047 33 5		S16	2047 30 6	2047 33 5	
		SM20	2047 33 9	2047 33 8		S20	2047 30 9	2047 30 8	
		SM25	2047 34 2	2047 34 1		S25	2047 31 2	2047 31 1	
		SM32	2047 34 5	2047 34 4		S32	2047 31 5	2047 34 4	
		SM40	2047 34 8	2047 34 7		S40	2047 31 8	2047 34 7	
		SM50	2047 35 1	2047 35 0		S50	2047 32 1	2047 35 0	
		SM63	2047 35 4	2047 35 3		S63	2047 32 4	2047 35 3	
Each pipe bend already has a sleeve screwed on.									
Pipe bend		SBM16	2047 50 1	2047 44 0		SB16	2047 48 5	2047 41 0	2047 42 5
		SBM20	2047 50 2	2047 44 1		SB20	2047 48 6	2047 41 1	2047 42 6
		SBM25	2047 50 3	2047 44 2		SB25	2047 48 7	2047 41 2	2047 42 7
		SBM32	2047 50 4	2047 44 3		SB32	2047 48 8	2047 41 3	2047 42 8
		SBM40	2047 50 5	2047 44 4		SB40	2047 48 9	2047 41 4	2047 42 9
		SBM50	2047 50 6	2047 44 5		SB50	2047 49 0	2047 41 5	2047 43 0
		SBM63	2047 50 7	2047 44 6		SB63	2047 49 1	2047 41 6	2047 43 1
Each pipe bend already has a sleeve screwed on.									
Pipe connection sleeve		SVM16	2047 47 0	2047 39 5		SV16	2047 45 5	2047 36 5	2047 38 0
		SVM20	2047 47 1	2047 39 6		SV20	2047 45 6	2047 36 6	2047 38 1
		SVM25	2047 47 2	2047 39 7		SV25	2047 45 7	2047 36 7	2047 38 2
		SVM32	2047 47 3	2047 39 8		SV32	2047 45 8	2047 36 8	2047 38 3
		SVM40	2047 47 4	2047 39 9		SV40	2047 45 9	2047 36 9	2047 38 4
		SVM50	2047 47 5	2047 40 0		SV50	2047 46 0	2047 37 0	2047 38 5
		SVM63	2047 47 6	2047 40 1		SV63	2047 46 1	2047 37 1	2047 38 6

OBO. Used by professionals



OBO BETTERMANN GmbH & Co. KG
P.O. Box 1120, 58694 Menden, Germany
www.obo-bettermann.com

Customer Service Germany
Tel. +49 (0)2373 89-1500
fax +49 (0)2373 89-7777
E-mail: info@obo-betterman.com

