

All in white:

The OBO WhiteLine



Pure joy: ECO Series and Quick-Pipe system in pure white

White is increasingly in demand for electrical installations. Particularly in places that are typically painted white, such as cellars or garages, the colour purity should not be disturbed in any way. That is why there is now the WhiteLine from OBO: the whole ECO range and the Quick-Pipe system are now also available in pure white. But of course Quick-Pipe and ECO are not only attractive on the outside: it goes right through. The refined, streamlined housing of the ECO junction boxes conceals many intelligent details, which enable them to be installed faster, more conveniently and therefore more cost efficiently – and at no higher price than for other products. Quick-Pipe combines the advantages of cable duct and installation pipe in an innovative, intelligent system. It allows clean and reliable surface installation of all kinds of cables on the wall and ceiling in record time, even in the same pipe. WhiteLine from OBO: you can see what you get.



Everything recommends ECO

Self-sealing cable entries, condensation openings, flexible terminal block fixing, large space for installation, secure and convenient mounting, capable of use in lines and attractive design: compared with ECO all the others are suddenly just boxes.

Ingenious locking system: Quick-Pipe system

The Quick-Pipe consists of only one part – and simply closes automatically after fitting. Quick-Pipe is suitable for a wide variety of tasks, for 230 V cables, but also for data cables, fibre-optic cables, coax cables, telephone cables and most particularly for pre-assembled cables with fitted plugs.

Model	Order No. pure white
ECO junction boxes	
ECO 10 VDE empty	2001 03 0
ECO 12 VDE empty	2001 03 3
ECO 14 VDE empty	2001 03 6
ECO 18 VDE empty	2001 03 9
OBO Quick-Pipe (supply length 2 m)	
2953/M16	2153 96 0
2953/M20	2153 96 3
2953/M25	2153 96 6
2953/M32	2153 96 9
Connection sleeve	
2953/M16-M	2153 97 1
2953/M20-M	2153 97 3
2953/M25-M	2153 97 5
2953/M32-M	2153 97 7
90° bend	
2953/M16-B	2153 98 0
2953/M20-B	2153 98 2
2953/M25-B	2153 98 4
2953/M32-B	2153 98 6
T-piece	
2953/M16-T	2153 99 2
2953/M20-T	2153 99 4
2953/M25-T	2153 99 6
2953/M32-T	2153 99 8
OBO Junior-Quick clip (Flame-retardant, non halogen-free)	
2950 F/M16	2154 64 1
2950 F/M20	2154 64 5
2950 F/M25	2154 65 0
2950 F/M32	2154 65 4

OBO. Used by professionals.



VBS TBS KTS BSS LFS UFS