

## Valid packages where you will find OBOpoints



Art. no.	Type	Art. no.	Type	Art. no.	Type
1361 16 3	733/M 16	2056 55 0	78/CE	2222 83 3	1996/40
1361 20 1	733/M 20	2056 56 9	78/CE	2222 86 8	1996/60
1361 29 5	733/M 25	2056 57 7	REIHENLUS	2227 42 8	2006/25
1361 38 4	733/M 32	2056 58 5	79/CE	2227 76 2	2009/35 SP
1361 48 1	733/M 40	2123 71 1	3079/14SO	2227 79 7	2009/45 SP
2000 01 6	A8 VDE leer	2123 73 8	3080/17SO	2228 43 2	2026/25 SP
2000 34 2	A11 VDE leer	2123 81 9	3080/17 SO	2228 44 0	2026/35 SP
2001 00 0	ECO 10	2123 82 7	3081/25 SO	2228 62 9	2025/25GR
2001 00 6	ECO 12	2123 85 1	3080/2/17	2228 72 6	2026/25GR
2001 01 2	ECO 14	2149 00 4	2955/M 16	2249 72 3	2037/20 SO
2001 01 8	ECO 18	2149 01 0	2955/M 20	2250 13 6	2037/13
2001 05 5	A6 LEER	2149 01 6	2955/M 25	2349 04 3	910/N5X25
2001 85 3	B9/TMLEER	2149 02 2	2955/M 32	2349 05 1	910/N 6
2003 01 5	UG60D	2149 02 8	2955/M 40	2349 07 8	910/N6X60
2003 01 9	UG60VD	2149 35 7	2955F/M20	2349 08 6	910/N 8
2003 04 3	UV70D	2149 36 3	2955F/M25	2349 10 8	910/N10X50
2003 11 2	UV 80K	2149 36 9	2955F/M32	2349 12 4	910/N12X60
2003 11 8	UV100K	2149 50 4	2955M16 SO	2351 02 1	910SD5X35
2003 22 3	UG60FD	2149 50 8	2955M20 SO	2351 05 6	910SD6X25
2003 22 7	UV70FD	2149 51 2	2955M25 SO	2351 06 4	910/SD 6x40
2003 41 4	HG60	2153 10 6	M-Quick 1	2351 09 9	910SD8X50
2003 42 2	HG60/2	2153 11 4	M-Quick 2	2351 21 8	910/SD-Q
2003 44 2	HV60	2153 13 0	M-Quick 3	2351 41 2	910/STP
2008 07 6	VBX25M LE	2153 15 7	M-Quick 4	3100 15 4	903/15
2008 11 4	VBX60M LE	2153 71 8	M-QU.ME16	3100 18 9	903/18
2008 97 1	VBX/MO	2153 72 6	M-QU.ME20	3105 01 6	903/RB 15
2022 86 4	V-TEC VM 16	2153 73 4	M-QU.ME25	3105 02 4	903/RB 18
2022 86 6	V-TEC VM 20	2153 82 9	2953M16 MG	3195 24 4	4758/4x30
2022 86 8	V-TEC VM 25	2153 83 1	2953M20 MG	3195 25 2	4758/4x35
2022 87 0	V-TEC VM 32	2153 86 4	2953M16 BG	3195 26 0	4758/4x40
2024 72 1	V-TEC11	2153 86 6	2953M20 BG	3341 05 4	1101/50
2024 74 8	V-TEC13	2153 87 2	2953M161G	3341 07 0	1101/70
2024 75 6	V-TEC16	2153 87 4	2953M201G	3342 05 0	1101/Z 50
2024 76 4	V-TEC21	2153 90 4	2953M16 GR	3342 07 7	1101/Z 70
2035 32 4	106 M 16	2153 91 2	2953M20 GR	3353 16 8	362/16
2035 33 2	106 M 20	2153 96 0	2953M16 WS	3353 18 4	362/18
2035 34 0	106 M 25	2153 96 3	2953M20 WS	3353 23 0	362/23
2035 35 9	106 M 32	2153 97 1	2953M16 MW	3353 30 3	362/30
2035 99 5	106/16 SO	2153 97 3	2953M20 MW	3353 40 0	362/40
2036 09 6	106/9	2153 98 0	2953M16 BW	3354 16 4	362/Z 16
2036 11 8	106/11	2153 98 2	2953M20 BW	3354 18 0	362/Z 18
2036 16 9	106/16	2197 80 4	1974/23	3354 23 7	362/Z 23
2036 21 5	106/21	2197 81 2	1974/30	3354 29 6	362/Z 30
2038 35 8	106/11 SO	2197 85 5	1974/2X12	3354 40 7	362/Z 40
2047 81 0	129 M 16	2197 86 3	1974/2X25	3360 23 7	500/23
2047 82 9	129 M 20	2204 90 8	2032/F	3360 29 6	500/30
2047 83 7	129 M 25	2204 91 6	2033/F	3361 23 3	500/23
2047 85 3	129 M 32	2204 97 5	2032/SP	3361 30 6	500/Z30
2054 48 5	61/325	2204 98 3	2033/SP	3366 23 5	511/23
2054 50 7	61/525	2204 99 1	2034/SP	3366 30 8	511/30
2054 52 3	61/825	2205 20 3	2031/ 8	3367 23 1	511/Z 23
2055 02 3	70/VDE	2205 21 1	2031/15	3367 30 4	511/Z 30
2056 07 0	72/CE	2205 23 8	2031/30	3453 82 0	948/166
2056 08 9	72/CE	2205 31 9	2031/F/ 8	3481 61 1	450/M4
2056 22 4	74/CE	2205 32 7	2031/F/15	3482 01 4	453
2056 23 2	74/CE	2205 33 5	2031/F/30	5015 07 3	1809
2056 37 2	76/CE	2205 38 6	2031/15 DF	5057 50 7	927/0
2056 38 0	76/CE	2205 39 4	2031/30 DF	5057 51 5	927/1

Please visit [www.obo-points.com](http://www.obo-points.com) for more detailed information



© OBO BETTERMANN Best.-Nr. 9177906 03/2007 EN

## Cash in points

Cash in all the OBOpoints you have collected for attractive prizes



Please visit [www.obo-points.com](http://www.obo-points.com) to see all prizes

[www.obo-points.com](http://www.obo-points.com)

## Collect OBOpoints Cash in points Win prizes



[www.obo-points.com](http://www.obo-points.com)

# OBOpoints

The OBO prize programme

[www.obo-points.com](http://www.obo-points.com)

How to enter the world of OBOpoints



## Collect OBOpoints

You will find OBOpoints in the OBO product packaging that is valid for this prize programme.



The code printed on the enclosed ticket is worth a certain number of OBOpoints, depending on the product. As soon as you have entered the code

under [www.obo-points.com](http://www.obo-points.com), the points value will be credited to your OBOpoints account.

Once you have collected sufficient OBOpoints, you can exchange them for exciting prizes.

Visit [www.obo-points.com](http://www.obo-points.com) for further information and register today. To thank you for registering, we will give you a starting credit of 2,500 OBOpoints.

## Win prizes

Every registered participant is entered into a competition. Win fantastic prizes from the latest range of bonus items.



You can view the prizes on offer by visiting [www.obo-points.com](http://www.obo-points.com).



## Register and take part

You can only take part in the OBOpoints bonus programme via the Internet at [www.obo-points.com](http://www.obo-points.com). You can enter your codes, manage your points balance and select attractive prizes.

### It couldn't be simpler:

- Register at [www.obo-points.com](http://www.obo-points.com)
- Secure your starting credit of 2,500 OBOpoints
- Collect and manage further OBOpoints
- Select prizes and cash in your OBOpoints

Please note that codes sent in by post will not be valid.

