


Technical data sheet

Cutting ring

Item number: 2029480



Rubber cutting ring (cuttable sealing ring) to DIN 46320 for cone cable gland.

Pg

NBR
SBR

Rubber mixture

Master data		
Item number	2029480	
Type	107 B PG48	
Description 1	Cutting ring	
Manufacturer	OBO	
Dimension	PG48	
Colour	Black	
Material	Rubber mixture	
Smallest sales unit	50	
Unit of quantity	Piece	
Weight	2.615 kg	
Weight unit	kg/100 pc.	
CO Footprint (GWP) Cradle-to-Gate	0,118 kg COe / 1 Piece	


Technical data sheet

Cutting ring

Item number: 2029480



Dimensions



Dimension D1	36 mm
Dimension D2	56.9 mm
Dimension D3	39 mm
Dimension D4	42 mm
Dimension D5	45 mm
Dimension H	14 mm

Technical data

Sealing area D, max.	45 mm
Sealing area D, min.	36 mm
Size	Pg 48
Size	M63