


# Technical data sheet

## Reduction, metric thread

Item number: 2030670



Reduction with metric internal and external thread for mounting plastic cable glands on enclosures. Protection class IP54 without additional connecting seal. Protection class up to IP68 possible with additional connecting seal, e.g. O-ring or flat sealing ring.



PA Polyamide

### Master data

|                                   |                        |
|-----------------------------------|------------------------|
| Item number                       | 2030670                |
| Type                              | 107 R M63-32 PA        |
| Description 1                     | Reduction              |
| Manufacturer                      | OBO                    |
| Dimension                         | M63-M32                |
| Colour                            | Light grey; RAL 7035   |
| Material                          | Polyamide              |
| Smallest sales unit               | 25                     |
| Unit of quantity                  | Piece                  |
| Weight                            | 3.07 kg                |
| Weight unit                       | kg/100 pc.             |
| CO Footprint (GWP) Cradle-to-Gate | 0,138 kg COe / 1 Piece |


# Technical data sheet

## Reduction, metric thread

Item number: 2030670



### Dimensions



|              |       |
|--------------|-------|
| Dimension E  | 75 mm |
| Dimension L  | 18 mm |
| Dimension L1 | 12 mm |
| Dimension L2 | 6 mm  |
| Dimension L3 | 18 mm |

### Technical data

|                                    |        |
|------------------------------------|--------|
| explosion-proof                    | no     |
| Thread type: External thread       | Metric |
| Thread type: Internal thread       | Metric |
| Thread length                      | 12 mm  |
| Thread dimension, metric, external | 63     |
| Thread dimension, metric, internal | 32     |
| Halogen-free                       | yes    |
| WAF                                | 68     |
| Nickel-plated                      | no     |