

Technical data sheet

Expansion piece, metric thread

Item number: 2088283



Extension made from brass with metric inner and outer thread to mount metal or plastic cable glands on housings. IP54 protection rating without additional connection sleeve. Protection rating of up to IP68 possible with additional connection seal, such as an O-ring or flat sealing ring.



Brass



Nickel-plated

Master data

Item number	2088283
Type	165 ADA M25-32
Description 1	Extension
Description 2	M - M
Manufacturer	OBO
Dimension	M25-M32
Material	Brass
Surface	Nickel-plated
Surface standard	
Smallest sales unit	50
Unit of quantity	Piece
Weight	2.71 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0709 kg COe / 1 Piece

Technical data sheet


Expansion piece, metric thread

Item number: 2088283



Dimensions

Dimension D	20.8 mm
Dimension E	35.8 mm
Dimension G1 (mm)	25
Dimension G2 (mm)	32
Dimension L	20.7 mm
Dimension L1	7.4 mm
Dimension L2	8 mm
Dimension L4	4 mm



Technical data

explosion-proof	no
Thread type: External thread	Metric
Thread type: Internal thread	Metric
Thread dimension, metric, external	25
Thread dimension, metric, internal	32
WAF	34
Nickel-plated	yes