

Technical data sheet

Expansion piece, metric thread

Item number: 2088285



Extension made from brass with metric inner and outer thread to mount metal or plastic cable glands on housings. IP54 protection rating without additional connection sleeve. Protection rating of up to IP68 possible with additional connection seal, such as an O-ring or flat sealing ring.



CuZn
37

Brass

N

Nickel-plated

Master data	
Item number	2088285
Type	165 ADA M40-50
Description 1	Extension
Description 2	M - M
Manufacturer	OBO
Dimension	M40-M50
Material	Brass
Surface	Nickel-plated
Surface standard	
Smallest sales unit	10
Unit of quantity	Piece
Weight	10.15 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,267 kg COe / 1 Piece

Technical data sheet


Expansion piece, metric thread

Item number: 2088285



Dimensions

Dimension D	33.8 mm
Dimension E	58 mm
Dimension G1 (mm)	40
Dimension G2 (mm)	50
Dimension L	30.5 mm
Dimension L1	8.2 mm
Dimension L2	12.5 mm
Dimension L4	6 mm



Technical data

explosion-proof	no
Thread type: External thread	Metric
Thread type: Internal thread	Metric
Thread dimension, metric, external	40
Thread dimension, metric, internal	50
WAF	52
Nickel-plated	yes