

Technical data sheet

Reduction, metric thread

Item number: 2089610



Reduction (Part H) in accordance with DIN 46320, with metric thread to DIN EN 60423 or ISO 68.

* Prices according to DEL notation.



Brass



Nickel-plated

Master data

Item number	2089610
Type	167 R MS M50-40
Description 1	Reduction
Manufacturer	OBO
Dimension	M50-M40
Material	Brass
Surface	Nickel-plated
Surface standard	
Smallest sales unit	25
Unit of quantity	Piece
Weight	10.25 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,2539 kg COe / 1 Piece


Technical data sheet

Reduction, metric thread

Item number: 2089610



Dimensions



Dimension D	57 mm
Dimension L1	10 mm
Dimension L2	4 mm

Technical data

explosion-proof	no
Thread type: External thread	Metric
Thread type: Internal thread	Metric
Thread length	10 mm
Thread dimension, metric, external	50
Thread dimension, metric, internal	40
Nickel-plated	yes