


Technical data sheet

Grip 10 flame-resistant

Item number: 2205388



Cable tidy with moulded fastening element, for mounting up to 10 cables NYM 3 x 1.5 mm² on walls or ceilings. Fastening with impact anchor or push-fit anchor. Fastening hole: Ø 6 mm. Recommended fastening distance of 250–400 cm when fully assigned, depending on the respective national specifications/norms. Flame resistant to DIN VDE 0471/DIN IEC 695 Part 2-1, test temperature 960 °C. Capacity: 2031/ 10 max. 10 cables NYM 3 x 1.5 mm²



PP Polypropylene

Master data

Item number	2205388
Type	2031 F 10
Description 1	Grip collecting clamp
Description 2	with arrangement contour,960°C
Manufacturer	OBO
Dimension	10x NYM3x1,5
Colour	Stone grey; RAL 7030
Material	Polypropylene
Smallest sales unit	50
Unit of quantity	Piece
Weight	1.41 kg
Weight unit	kg/100 pc.


Technical data sheet

Grip 10 flame-resistant

Item number: 2205388



Dimensions



Technical data

No. of conductors NYM 3 x 1.5	10
Flame-resistant version	yes
Breaking load	0.32 kN
Maintain electrical functions	no
Halogen-free	yes
With anchor	no