

Technical data sheet

Fixed earthing terminal with axis and double thread A4

Item number: 5420022



- For connection to earthing systems, conductors and reinforcements
- Contact plate: Ø 80 mm made of stainless steel, rustproof (V4A)
- With M10 and M12 thread
- Incl. plastic cover for simple installation
- With 180 mm connection bolt (V4A)



A4 Stainless steel

Master data		
Item number	5420022	
Type	205 DG L180 V4A	
Description 1	Earthing fixed point with axis	
Description 2	and double thread	
Manufacturer	OBO	
Dimension	M10/M12	
Material	Stainless steel	
Smallest sales unit	10	
Unit of quantity	Piece	
Weight	23.4 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	1,4557 kg CO2e / 1 Piece	

Dimensions		
		Length
		180 mm

Technical data sheet

Fixed earthing terminal with axis and double thread A4

Item number: 5420022



Technical data

Connection axis	180 mm
Lightning current carrying capacity	H/100 kA
Diameter of the connection plate	80 mm
Thread	M10/M12
Short-circuit current (50 HZ)(1 s; ≤300°C)	3.3 kA
Material of the connection strap	Stainless steel, rustproof (V4A)