

# Technical data sheet

## Suspension eyelet

Item number: 3464067



M6 suspension lug



|           |                   |
|-----------|-------------------|
| <b>Zn</b> | Die-cast zinc     |
| <b>G</b>  | Electrogalvanized |

### Master data

|                                    |                            |
|------------------------------------|----------------------------|
| Item number                        | 3464067                    |
| Type                               | 2085 M6 G                  |
| Description 1                      | Suspension lugs            |
| Manufacturer                       | OBO                        |
| Dimension                          | M6                         |
| Material                           | Die-cast zinc              |
| Surface                            | Electrogalvanized          |
| Surface standard                   | EN ISO 19598 / EN ISO 4042 |
| Smallest sales unit                | 50                         |
| Unit of quantity                   | Piece                      |
| Weight                             | 3.9 kg                     |
| Weight unit                        | kg/100 pc.                 |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,1822 kg COe / 1 Piece    |

### Dimensions

|               |         |
|---------------|---------|
| Dimension b   | 8 mm    |
| Dimension BØ  | 15 mm   |
| Dimension D   | 40 mm   |
| Dimension d Ø | 24 mm   |
| Dimension L   | 44.5 mm |

# Technical data sheet

## Suspension eyelet

Item number: 3464067



### Technical data

|               |        |
|---------------|--------|
| Breaking load | 1.1 kN |
| Thread metric | 6      |