


Technical data sheet

Cover clip for WDK trunking, trunking width 130 mm

Item number: 6023525



Cover clip for better and easier laying of lines in the WDK trunking. The cover fixing device can be moved along the entire length of the trunking. The cover clip is locked on one side and moved forward. This provides a 30° opening, meaning that cable routing is very simple. From trunking widths of 110 mm, the cover clips can also be used as a mounting aid.




PVC Polyvinylchloride

Master data

Item number	6023525
Type	2370 130
Description 1	Cover fixing device
Manufacturer	OBO
Dimension	130mm
Colour	Light grey; RAL 7035
Material	Polyvinylchloride
Smallest sales unit	20
Unit of quantity	Piece
Weight	2.2 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,089 kg CO2e / 1 Piece

Dimensions



Length	36 mm
Width	116.2 mm
Dimension a	116.2 mm
Dimension b	36 mm

Technical data sheet

Cover clip for WDK trunking, trunking width 130 mm

Item number: 6023525



Technical data

Fastening type	Lockable
Maintain electrical functions	no
Halogen-free	no
With equipotential bonding	no
Cover width	130 mm
Protection rating	IP30
Protection rating IK code	IK04
Self-extinguishing	yes
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C