

Technical data sheet

Diagonal connector for A4 round conductor

Item number: 5313012



- Meets the requirements of VDE 0185-305-3 (IEC/ EN 62305-3)
- To connect round conductors 8–10 mm
- Mounted with 2 truss-head bolts M10 x 30 and 2 hexagonal bolts M10



A4 Stainless steel

Master data

Item number	5313012
Type	2760 S8 V4A
Description 1	Connecting strap
Manufacturer	OBO
Dimension	RD 8-10
Material	Stainless steel
Smallest sales unit	3600
Unit of quantity	Piece
Weight	20.6 kg
Weight unit	kg/100 pc.

Technical data sheet



Diagonal connector for A4 round conductor

Item number: 5313012



Dimensions

Dimension A 101 mm



Technical data

Type of fastening screw	Gutter bolt
Type of connector	Connectors
Lightning current carrying capacity	H/100 kA
Suitable for connection	Round conductor Rd 8–10 / Rd 8–10
Fit	Rd 8-10 mm
Intermediate plate	no
Clamping range, max.	10 mm
Clamping range, min.	8 mm