


# Technical data sheet

Quick clip, for push-fit anchors, light grey

Item number: 2149710



Flush-mounted clip to accept metric steel armoured pipes and heavy-duty insulating pipes, as well as Quick Pipe electrical installation pipes. Universal fastening options on walls and ceilings, both in indoor and protected outdoor areas. With slot for side alignment during mounting with wood screw or knock-in anchor. Toolless pipe mounting. Can also be arranged with OBO Multi-Quick or starQuick clip. M16 - M32 size can be screwed onto M6 thread. Recommended fastening spacing 50–60 cm, for max. extraction values F at a room temperature of 20 °C, see the table.



Acrylonitrile butadiene styrene

## Master data

Item number	2149710
Type	2957 M19-20
Description 1	Quick clip
Manufacturer	OBO
Dimension	M19-20
Colour	Light grey; RAL 7035
Material	Acrylonitrile butadiene styrene
Smallest sales unit	100
Unit of quantity	Piece
Weight	0.403 kg
Weight unit	kg/100 pc.


# Technical data sheet

Quick clip, for push-fit anchors, light grey

Item number: 2149710



## Dimensions



Dimension A	30.3 mm
Dimension B	16 mm
Dimension C	13.3 mm
Dimension D	18.6 mm
Dimension E	9 mm
Dimension F	4.2 mm
Dimension h	7 mm
Dimension H	30 mm

## Technical data

Expandable	yes
Number of cables/pipes	1
Fastening type	Screw hole
Closed	no
Halogen-free	yes
With inlay	no
Nominal size	M19-20
Clamping range D, max.	20 mm
Clamping range D, min.	19 mm
UV-resistant	no