

Technical data sheet

Clamping shoe

Item number: 5325315



- With Ø 11 mm attaching hole
- 2 hexagonal bolts M8 x 16
- Bolts hot-dip galvanised steel and clamping element hot dipped galvanised cast steel

SG	cast steel
F	Hot galvanized

Master data

Item number	5325315
Description 1	Clamping shoe
Manufacturer	OBO
Dimension	10mm
Material	cast steel
Surface	Hot galvanized
Surface standard	DIN 267, Teil 10
Smallest sales unit	25
Unit of quantity	Piece
Weight	9.65 kg
Weight unit	kg/100 pc.


Technical data sheet

Clamping shoe

Item number: 5325315



Dimensions



Technical data

Type of fastening screw	Hexagonal bolt
Type of connector	Clamping shoe
Fit	Rd 10 mm