


Technical data sheet

Cylinder head bolt G

Item number: 3153096



Cylinder head bolt according to ISO 1207 with metric thread. Drive slot M6 x 10 mm.



St Steel

G Electrogalvanized

Master data

Item number	3153096
Type	341 M6x10 G
Description 1	Cylinder head screw
Description 2	slot drive
Manufacturer	OBO
Dimension	M6x10mm
Material	Steel
Surface	Electrogalvanized
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	100
Unit of quantity	Piece
Weight	0.349 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,0096 kg COe / 1 Piece


Technical data sheet

Cylinder head bolt G

Item number: 3153096



Dimensions



Dimension	M6 x 10
Length	10 mm

Technical data

Thread	M6
Thread metric	6
Head shape	Cylinder head
With flange	no
With nut	no
With washer	no
Screw system	Screw slot
Self-locking	no
Full thread	yes
Left thread	no