

Technical data sheet

Ceiling hook

Item number: 3470237



Ceiling hook M6 x 125 mm



St Steel

G Electrogalvanized

Master data

Item number	3470237
Type	867 M6X125 G
Description 1	Ceiling hook
Manufacturer	OBO
Dimension	M6x125mm
Material	Steel
Surface	Electrogalvanized
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	100
Unit of quantity	Piece
Weight	2.76 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0616 kg COe / 1 Piece

Dimensions



Length	125 mm
Dimension d Ø	5.2 mm
Dimension L	85 mm

Technical data sheet

Ceiling hook

Item number: 3470237



Technical data

Breaking load	0.8 kN
Thread	M6
Thread length	85 mm
hook diameter	16 mm
Plastic-covered	no