

# Technical data sheet

## Screw-in nipple, metric thread, with perforation membrane

Item number: 2032380



With perforation membranes, the opening D is pre-marked, but closed.  
Grip seal to screw into metric thread to IEC 423.  
With self-sealing cone at the end of the thread, therefore no connection thread sealing ring required.  
Protection rating achievable with careful mounting: IP54.  
With perforation membranes, the opening D is pre-marked, but closed.



**PE** Polyethylene

Master data	
Item number	2032380
Type	90 M16 GE
Description 1	Screw-in nipple
Description 2	closed version
Manufacturer	OBO
Dimension	M16
Colour	Light grey; RAL 7035
Material	Polyethylene
Smallest sales unit	100
Unit of quantity	Piece
Weight	0.192 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0042 kg COe / 1 Piece


# Technical data sheet

## Screw-in nipple, metric thread, with perforation membrane

Item number: 2032380



### Dimensions



Dimension D	5 mm
Dimension E	20 mm
Dimension L1	8 mm
Dimension L2	6 mm

### Technical data

Thread length	8 mm
Size	M16
Halogen-free	yes
WAF	16
Protection rating	IP54