

Technical data sheet

Screw-in nipple, metric thread, with opening

Item number: 2032015



With open cable entry.

Grip seal to screw into metric thread end to IEC 423.

With self-sealing cone at the end of the thread, therefore no connection thread sealing ring required.

Protection rating achievable with careful mounting: IP54.
With open cable entry.



PE Polyethylene

Master data

Item number	2032015
Type	90 M20 OF
Description 1	Screw-in nipple
Description 2	open version
Manufacturer	OBO
Dimension	M20
Colour	Light grey; RAL 7035
Material	Polyethylene
Smallest sales unit	100
Unit of quantity	Piece
Weight	0.268 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,0072 kg COe / 1 Piece


Technical data sheet

Screw-in nipple, metric thread, with opening

Item number: 2032015



Dimensions



Dimension D	7 mm
Dimension E	24 mm
Dimension L1	10 mm
Dimension L2	6 mm

Technical data

Thread length	10 mm
Size	M20
Halogen-free	yes
WAF	21
Protection rating	IP54