

Technical data sheet

Steel wire tensioning rope 957

Item number: 5303203



Steel wire tensioning rope, galvanised with fibre inlay (hemp core).
Cable Ø 2–6 mm: Round flexible cable 6 x 7 to DIN 3055.
Cable Ø 8–10 mm: Round flexible cable 6 x 19 to DIN 3060.
Minimum break load 1,770 N/mm².



St	Steel
G	Electrogalvanized

Master data

Item number	5303203
Type	957 2,0x100 G S
Description 1	Steel wire tensioning cable
Description 2	100 m roll, silver
Manufacturer	OBO
Dimension	Ø2,0mmx100m
Material	Steel
Surface	Electrogalvanized
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	1
Unit of quantity	Piece
Weight	180 kg
Weight unit	kg/100 pc.

Dimensions

Dimension b	110 mm
Dimension D1	190 mm
Dimension L	100,000 mm

Technical data sheet

Steel wire tensioning rope 957

Item number: 5303203



Technical data

Breaking load	2.8 kN
in rings	100 m
Cable diameter	2 mm
Support load	0.6 N
Support load	0.6 kN