

Technical data sheet

Screw-in anchor with M6 thread

Item number: 3133028



With wood screw shank and M6 thread.




St	Steel
G	Electrogalvanized

Master data

Item number	3133028
Type	985 M6 25
Description 1	Screw-in anchors
Manufacturer	OBO
Dimension	M6x25mm
Material	Steel
Surface	Electrogalvanized
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	100
Unit of quantity	Piece
Weight	0.412 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0101 kg COe / 1 Piece

Dimensions



Length	25 mm
Dimension D	4.3 mm
Dimension G	M6 mm
Dimension L	35 mm
Dimension L1	25 mm

Technical data sheet

Screw-in anchor with M6 thread

Item number: 3133028



Technical data

Hardened	no
Head shape	external thread
Shank diameter	4.3 mm
Screw system	Miscellaneous
Two-compartment	no