

# Technical data sheet

## Ceiling bracket 13 FT

Item number: 6363908



Suspension bracket for cable support systems to fasten directly under the ceiling or as a suspension with threaded rods M10.



|           |                    |
|-----------|--------------------|
| <b>St</b> | Steel              |
| <b>FT</b> | Hot-dip galvanised |

### Master data

|                     |                    |
|---------------------|--------------------|
| Item number         | 6363908            |
| Type                | AHB 150 13 FT      |
| Description 1       | Suspension bracket |
| Description 2       | flat steel         |
| Manufacturer        | OBO                |
| Dimension           | B150mm             |
| Colour              | zinc               |
| Material            | Steel              |
| Surface             | Hot-dip galvanised |
| Surface standard    | DIN EN ISO 1461    |
| Smallest sales unit | 1                  |
| Unit of quantity    | Piece              |
| Weight              | 77.2 kg            |
| Weight unit         | kg/100 pc.         |


# Technical data sheet

## Ceiling bracket 13 FT

Item number: 6363908



### Dimensions



|        |        |
|--------|--------|
| Width  | 181 mm |
| Height | 130 mm |
| Maß W  | 165 mm |

### Technical data

|                                  |                              |
|----------------------------------|------------------------------|
| Version for                      | Suspension bracket (C clamp) |
| F in kN ceiling                  | 0.7 kN                       |
| Maintain electrical functions    | no                           |
| for width max.                   | 150 mm                       |
| for width min.                   | 150                          |
| Suitable for metric threaded rod | 10                           |
| Suitable for mesh cable tray     | no                           |
| Suitable for cable ladder        | no                           |
| Suitable for cable tray          | yes                          |
| Suitable for tray/ladder width   | 150 mm                       |
| Hole diameter                    | 11 mm                        |
| Material thickness               | 8 mm                         |
| Tray fastening                   | Screw-on                     |
| Adjustable                       | no                           |