

Technical data sheet

Spacer clip 733 A4

Item number: 1362908



Spacer clip for the installation of pipes and cables on walls, ceilings and floors.
With self-locking cover. Fastening via slot.

Approved for the maintenance of electrical function according to DIN 4102 Part 12, maintenance of electrical function classes E 30 to E 90.



A4 Stainless steel

Master data		
Item number	1362908	
Type	ASL 733 14 A4	
Description 1	Distance saddle	
Description 2	with slot	
Manufacturer	OBO	
Dimension	12-14mm	
Material	Stainless steel	
Smallest sales unit	25	
Unit of quantity	Piece	
Weight	1.973 kg	
Weight unit	kg/100 pc.	
CO Footprint (GWP) Cradle-to-Gate	0,1573 kg COe / 1 Piece	


Technical data sheet

Spacer clip 733 A4

Item number: 1362908



Dimensions



Dimension A	41 mm
Dimension B	29 mm
Dimension b	14 mm
Dimension D	14 mm
Dimension d max.	14 mm
Dimension d min.	12 mm
Dimension L	10 mm
Dimension s	8 mm
Dimension t1 (mm)	1.25
Dimension t2 (mm)	1.5
Dimension x	3 mm

Technical data

Distance to the wall	yes
Number of cables/pipes	1
Version for	Closed
Fastening type	Screw hole
For diameter	12 - 14
Suitable in fire protection area	no
Halogen-free	yes
Plastic-covered	no
Material thickness	1.5 mm
Clamping range D, max.	14 mm
Clamping range D, min.	12 mm
UV-resistant	yes