

Technical data sheet

Junction box A 18

Item number: 2000422



Protection rating IP55, rated voltage 690 V, nominal cross-section 2.5 mm², 10 entries for cable diameter 5–14 mm

8 entries for cable diameter 5–11 mm.

Clamshell.

Dimensions: 125 x 100 x 40 mm

Clear internal dimensions: 115 x 90 x 35 mm

1 cut-out tool for every 10 boxes



PE Polyethylene

Master data

Item number	2000422
Type	A 18 HF RW
Description 1	Junction box
Manufacturer	OBO
Dimension	125x100x38
Colour	Pure white; RAL 9010
Material	Polyethylene
Smallest sales unit	10
Unit of quantity	Piece
Weight	6.957 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,1968 kg COe / 1 Piece

Technical data sheet

Junction box A 18

Item number: 2000422



Technical data

Permitted temperature range, min.	-5 °C
Transparent lid	no
Castable	no
Sealing compound supplied	no
Weatherproof	no
Junction box cover version	Blanking lid