

Technical data sheet

90° bend for PYROLINE® Con S BSKH09-K0506 fire protection duct

Item number: 7215604



90° bend for PYROLINE® Con S fire protection duct, type BSKH09-K0506, consisting of fibreglass lightweight concrete which is resistant to water and frost for the creation of horizontal changes of direction of the duct. Mounted connectors ensure quick mounting in situ, whilst loosely placed covers ensure quick inspection and reassignment.

Including connection screws and sealing strips.
Including connection screws and sealing strip.



Fibreglass lightweight concrete

Master data

Item number	7215604
Description 1	90° bend
Description 2	for BSKH09-K0506
Manufacturer	OBO
Dimension	50x60
Colour	Grey
Material	Fibreglass lightweight concrete
Smallest sales unit	1
Unit of quantity	Piece
Weight	705 kg
Weight unit	kg/100 pc.


Technical data sheet

90° bend for PYROLINE® Con S BSKH09-K0506 fire protection duct

Item number: 7215604



Dimensions



External dimensions	188 x 140
Internal dimensions	60 x 50
Length	314 mm
Width	354 mm
Height	140 mm
Dimension B	188 mm
Dimension b	60 mm
Dimension h	50 mm
Dimension H	140 mm
Dimension L	290 mm

Technical data

Number of flammable sides	4
Cover fastening	Loose
Fire resistance class E – function maintenance	30
Fire resistance class I – installation duct	90
With perforation	no
Partitions possible	yes
Jacketing	Without
Material of the insulation	Glass-fibre lightweight concrete
Angle of the bend	90 °