

Technical data sheet

T piece for PYROLINE® Con S BSKH09-K1021 fire protection duct


Item number: 7215645



T piece for PYROLINE® Con S fire protection duct, type BSKH09-K1021, consisting of fibreglass lightweight concrete which is resistant to water and frost, for the creation of T branches of the duct. Mounted connectors ensure quick mounting in situ, whilst loosely placed covers ensure quick inspection and reassignment.

Including connection screws and sealing strips.

Including connection screws and sealing strip.



Fibreglass lightweight concrete

Master data

Item number	7215645
Description 1	T piece
Description 2	for BSKH09-K1021
Manufacturer	OBO
Dimension	105x210
Colour	Grey
Material	Fibreglass lightweight concrete
Smallest sales unit	1
Unit of quantity	Piece
Weight	2059 kg
Weight unit	kg/100 pc.


Technical data sheet

T piece for PYROLINE® Con S BSKH09-K1021 fire protection duct

Item number: 7215645



Dimensions



External dimensions	338 x 195
Internal dimensions	210 x 105
Length	640 mm
Width	454 mm
Height	195 mm
Dimension B	338 mm
Dimension b	210 mm
Dimension h	105 mm
Dimension H	195 mm
Dimension L	590 mm
Dimension l	444 mm

Technical data

Number of flammable sides	4
Fire resistance class E – function maintenance	30
Fire resistance class I – installation duct	90
With perforation	no
Partitions possible	yes
Jacketing	Without
Material of the insulation	Glass-fibre lightweight concrete