

Technical data sheet

Bolt tie BZ

Item number: 3498358



Bolt tie BZ for the anchoring of medium-duty to heavy-duty loads, both in cracked and non-cracked concrete. It combines high approved loads with small edge distances and axial spacings.
European Technical Approval ETA-99/0010, including characteristic values under fire exposure to fire resistance R 120.

Proof of suitability in the case of seismic impacts, categories C1 and C2.

Shock approval by the Federal Office for Civil Protection in Bern, Switzerland.




St	Steel
G	Electrogalvanized

Master data

Item number	3498358
Description 1	Wedge anchor BZ
Manufacturer	OBO
Dimension	M12x255mm
Colour	zinc
Material	Steel
Surface	Electrogalvanized
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	20
Unit of quantity	Piece
Weight	22.4 kg
Weight unit	kg/100 pc.

Dimensions



Length	255 mm
Dimension L	255 mm

Technical data sheet

Bolt tie BZ

Item number: 3498358



Technical data

Version for	For knocking in
Anchor/nail/bolt version	Spreading anchor
Drill hole depth	90 mm
Drill hole diameter, min.	12 mm
Thread	M12
Thread metric	12
Thread type	Metric
Clamping strength	160 mm
Approvals available	yes
Permitted load range, tension zone	7.6
Clamping range, min.	160 mm

Standard anchoring depth

	Bore hole Ø			
	mm			
46	8	60	100	2,4
60	10	75	75	4,3
60	10	75	100	4,3
70	12	90	15	7,6
70	12	90	85	7,6
70	12	90	105	7,6
70	12	90	160	7,6
85	16	110	15	11,9