


Technical data sheet

Rung CK 40

Item number: 6008224



CK40 rung for use in heavy-duty vertical ladders and in IS 8 supports.
The maximum rung load is 175 kg.



St

Steel

FT

Hot-dip galvanised

Master data

Item number	6008224
Description 1	C-frame
Description 2	for IS 8 support
Manufacturer	OBO
Dimension	B154mm
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	62.3 kg
Weight unit	kg/100 pc.


Technical data sheet

Rung CK 40

Item number: 6008224



Dimensions



lampDimension WxH	40 x 22,5 mm
Length	154 mm
Width	154 mm
Height	100 mm

Technical data

Material thickness	2 mm
Slot width	18 mm