

Technical data sheet

Deskbox DBK, 3 sockets, 2x RJ45 Cat. 6

Item number: 6116806



Foldable Deskbox with connection cable for fixed installation in a tabletop, housing made of brushed stainless steel with brush bar as cable outlet. Mounting is done via an installation opening 245 x 157 mm in the tabletop.

Equipped with:

- three black protective contact sockets of 60° plug-in direction, including 3.0 m power cable with angular connector CEE 7/7.

- two data technology couplings RJ45 on RJ45, 1:1 switched, Cat. 6 shielded.

Note: Can be used in tabletops of up to 50 mm thickness.

The ready-for-connection type DBK Deskbox is particularly suitable for the direct supply of workstations with energy, communication and data technology connections.

A2 Stainless steel

Master data

Item number	6116806
Type	DBK2-D4 D3S2K
Description 1	Deskbox, foldable
Description 2	for installation in table tops
Manufacturer	OBO
Dimension	260x167x68
Material	Stainless steel
Smallest sales unit	1
Unit of quantity	Piece
Weight	163.86 kg
Weight unit	kg/100 pc.

Dimensions



Length	260 mm
Width	167 mm

Technical data sheet

Deskbox DBK, 3 sockets, 2x RJ45 Cat. 6

Item number: 6116806



Technical data

Number of audio connections	0
Number of CAT 5 connections	0
Number of CAT 5E connections	0
Number of CAT 6 connections	2
Number of USB connections	0
Number of VGA connections	0
Number of HDMI connections	0
Number of SCHUKO sockets	3
Version for	Installation
Extendable	no
Shape	Rectangular
Foldable	yes
Length of the supply cable	3 m
Surge protection	no