

Technical data sheet

Deskbox DBK, 2 sockets, HDMI, 2x RJ45 Cat. 6

Item number: 6116810



Foldable Deskbox with connection cable for fixed installation in a tabletop, housing made of brushed stainless steel with brush bar as cable outlet. Mounting is done via an installation opening 245 x 157 mm in the tabletop.

Equipped with:

- Two black protective contact sockets of 60° plug-in direction, including 3.0 m power cable with angular connector CEE 7/7.
- One HDMI 1.3 socket, including 3.0 m connection cable with plug.
- Two data technology couplings RJ45 on RJ45, 1:1, Cat. 6 shielded.

Note: Can be used in tabletops of up to 50 mm thickness.

The ready-for-connection type DBK Deskbox is particularly suitable for the direct supply of workstations with energy, communication and data technology connections.

A2 Stainless steel

Master data

Item number	6116810
Type	DBK2-M4H D2S2K
Description 1	Deskbox, foldable
Description 2	for installation in table tops
Manufacturer	OBO
Dimension	260x167x68
Material	Stainless steel
Smallest sales unit	1
Unit of quantity	Piece
Weight	173.76 kg
Weight unit	kg/100 pc.

Dimensions



Length	260 mm
Width	167 mm

Technical data sheet

Deskbox DBK, 2 sockets, HDMI, 2x RJ45 Cat. 6

Item number: 6116810



Technical data

Number of audio connections	0
Number of CAT 5 connections	0
Number of CAT 5E connections	0
Number of CAT 6 connections	2
Number of USB connections	0
Number of VGA connections	0
Number of HDMI connections	1
Number of SCHUKO sockets	2
Version for	Installation
Extendable	no
Shape	Rectangular
Foldable	yes
Length of the supply cable	3 m
Surge protection	no