

Technical data sheet

Cover DBV 110 400 F FT for falling vertical bend.

Item number: 7131746



Cover for falling vertical bends of side height 110 mm.
The fastening is guaranteed by the overlap of the cable tray covers. The cover can also be fastened using cover clamps.



- St** Steel
- FT** Hot-dip galvanised

Master data

Item number	7131746
Type	DBV 110 400 F FT
Description 1	Cover for 90° vertical bend
Description 2	falling
Manufacturer	OBO
Dimension	B400mm
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	195 kg
Weight unit	kg/100 pc.

Technical data sheet

Cover DBV 110 400 F FT for falling vertical bend.

Item number: 7131746



Dimensions



Height	110 mm
Plate thickness	0.03 in
Plate thickness	0.75 mm

Technical data

Bend (angle)	90°
Fastening type	Sash lock
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	no
Suitable for cable tray	yes
Change of direction	Vertical, falling
Rustproof steel, pickled	no
Hinged	no