

# Technical data sheet

## Cover for 90° vertical bend, rising, FT

Item number: 7131712



Cover for all rising vertical bends.

The fastening is guaranteed by the overlap of the cable tray covers. The cover can also be fastened using cover clamps.



**St** Steel

**FT** Hot-dip galvanised

### Master data

Item number	7131712
Type	DBV 200 S FT
Description 1	Cover for 90° vertical bend
Description 2	rising
Manufacturer	OBO
Dimension	B200mm
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	65.2 kg
Weight unit	kg/100 pc.


# Technical data sheet

## Cover for 90° vertical bend, rising, FT

Item number: 7131712



### Dimensions



Width	200 mm
Plate thickness	0.75 mm
Dimension B	200 mm

### Technical data

Bend (angle)	90°
Fastening type	Cover clamp
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	no
Suitable for cable tray	yes
Change of direction	Vertical rising
Rustproof steel, pickled	no
Hinged	no