


# Technical data sheet

## Unperforated cover A2

Item number: 6052834



Cover for cable trays and mesh cable trays.  
Transverse bead from 500 mm width.  
When using covers outdoors, additional measures against the influence of wind must be taken.



**A2** Stainless steel

**2B** Bright, treated

Master data		
Item number	6052834	
Description 1	Unperforated cover	
Description 2	for cable tray and ladder	
Manufacturer	OBO	
Dimension	300x3000	
Colour	stainless steel	
Material	Stainless steel	
Surface	Bright, treated	
Surface standard		
Smallest sales unit	3	
Unit of quantity	Metre	
Weight	256 kg	
Weight unit	kg/100 m	

# Technical data sheet

## Unperforated cover A2

Item number: 6052834



### Dimensions



Length	3,000 mm
Length	10 ft
Width	300 mm
Width	12 in
Height	35 mm
Plate thickness	0.04 in
Plate thickness	1 mm
Dimension B	300 mm
Dimension H	15 mm

### Technical data

Fastening type	Cover clamp
Maintain electrical functions	no
Suitable for mesh cable tray	yes
Suitable for cable ladder	yes
Suitable for cable tray	yes
Rustproof steel, pickled	no