

# Technical data sheet

Data technology support, 1 module, straight outlet, type F

Item number: 6119220



Data technology support with straight outlet and locking slider to accept two data technology connection modules. The locking fastening is suitable for horizontal and vertical installation in the system environment.

The type F data technology support is suitable for accepting the following data connection modules: Avaya/Systimax: M series.  
For installation in Rapid 45 and Rapid 80 device installation trunking, ISS service poles and underfloor systems.

**PC** Polycarbonate

Master data		
Item number	6119220	
Description 1	Data technology support	
Description 2	f. 2 connection modules type F	
Manufacturer	OBO	
Dimension	45x45mm	
Colour	Pure white; RAL 9010	
Material	Polycarbonate	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	1.1 kg	
Weight unit	kg/100 pc.	


# Technical data sheet

Data technology support, 1 module, straight outlet, type F


Item number: 6119220



## Dimensions



Width	45 mm
Height	45 mm



## Technical data

Number of units	1
Surface version	Matt
Fastening type	Lock
Labelling panel	With labelling panel
Halogen-free	yes
Hinged cover	no
Lamp-wire connector	no
With printed label	no
With dust protection	yes
Mounting opening	Type F
Protection rating	IP20
Depth	9 mm
Support ring	no
Transparent	no
Use	Installable data connector
Strain relief option	no
Combination	Basic element with central cover plate