

# Technical data sheet

## Data technology support, 1 module, slanting outlet, type PA

Item number: 6119266



Data technology support with slanting outlet and locking slider to accept two data technology connection modules with RJ45 socket. The locking fastening is suitable for horizontal and vertical installation in the system environment. Type PA has a special module seat and is designed for indirect fastening of the data connection modules in the mounting opening.

The type PA data technology support is suitable for accepting the following data connection modules: Panduit: Mini-Com.  
For installation in Rapid 45 and Rapid 80 device installation trunking, ISS service poles and underfloor systems.

**PC** Polycarbonate

### Master data

Item number	6119266
Description 1	Data technology support
Description 2	f. 2 connection modules type P
Manufacturer	OBO
Dimension	45x45mm
Colour	Aluminium painted
Material	Polycarbonate
Smallest sales unit	1
Unit of quantity	Piece
Weight	1.5 kg
Weight unit	kg/100 pc.


# Technical data sheet

Data technology support, 1 module, slanting outlet, type PA

Item number: 6119266



## Dimensions



Width	45 mm
Height	45 mm

## Technical data

Number of units	1
Surface version	Matt
Fastening type	Lock
Labelling panel	With labelling panel
Halogen-free	yes
Hinged cover	no
Lamp-wire connector	no
With printed label	no
With dust protection	yes
Mounting opening	Type PA
Protection rating	IP20
Depth	26 mm
Support ring	no
Transparent	no
Use	Installable data connector
Strain relief option	no
Combination	Basic element with central cover plate