

Technical data sheet

Earthing terminal with fastening thread

Item number: 6404006



Earthing terminal for fastening the equipotential bonding wire to the cable support system. M12 threaded pin with slot.

Suitable for conductor cross sections of 4–50 mm².



CuZn
37 Brass

Master data

Item number	6404006
Type	EKL 25 M6
Description 1	Earthing terminal
Description 2	with fastening thread M6
Manufacturer	OBO
Dimension	4-50mm ²
Colour	Brass
Material	Brass
Smallest sales unit	50
Unit of quantity	Piece
Weight	3.1 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0777 kg COe / 1 Piece

Dimensions

Dimension L	0.87 in
Dimension L	22 mm
Dimension I	8 mm

Technical data sheet

Earthing terminal with fastening thread

Item number: 6404006



Technical data

Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	yes
Suitable for cable tray	yes
Thread	M6
With screw accessories	no
Cross-section	50 mm ²
Rustproof steel, pickled	no
WAF	18
Connection type	With pin/drill hole