

Technical data sheet

2-component fire protection foam PYROSIT® NG

Item number: 7203800



PYROSIT® NG 2-component fire protection foam in a cartridge, including 2 mixing tubes.

To create cable and combination insulation in interior areas; always process the coaxial cartridge 5:1 with FBS-PH or FBS-PA cartridge pistols.

In dry, frost-free rooms, the cartridge can be stored closed and standing upright at temperatures from +5 °C to +30 °C for up to 12 months.

Processing of products containing diisocyanate is subject to training in accordance with REACH ordinance (EG) 1907/2006, as amended by Regulation (EU) 2020/1149 of 4.8.2020. The training can be carried out online. Information on this can be found in the technical info under downloads on the product.



2-component PU fire protection foam

Master data

Item number	7203800
Description 1	Fire protection foam
Description 2	in a cartridge
Manufacturer	OBO
Dimension	380ml
Colour	rust red
Material	2-component PU fire protection foam
Smallest sales unit	1
Unit of quantity	Piece
Weight	64.6 kg
Weight unit	kg/100 pc.

Technical data

Version for	Fire protection foam
Contents	380 ml
Delivery form	Cartridge