


Technical data sheet

Truss-head bolt with combination nut, V2A

Item number: 3175625



Truss-head bolt with square neck and combination nut.



A2	Stainless steel
2B	Bright, treated

Master data	
Item number	3175625
Type	FRSB M10x25 A2
Description 1	Truss-head bolt
Description 2	with combination nut
Manufacturer	OBO
Dimension	M10x25/25mm
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	50
Unit of quantity	Piece
Weight	3.7 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,1854 kg COe / 1 Piece


Technical data sheet

Truss-head bolt with combination nut, V2A

Item number: 3175625



Dimensions



Length	25 mm
Dimension D	10 mm
Dimension L	25 mm

Technical data

Thread metric	10
Thread type	Metric
Head shape	Flat round head with square
With flange	no
With nut	yes
With washer	no
Screw system	Miscellaneous
Self-locking	no
Full thread	yes
Left thread	no