


Technical data sheet

G mesh cable tray Magic® 75 A2

Item number: 6005553



G-shaped mesh cable tray made of spot-welded steel wire with different side heights and widths.

Direct wall or ceiling mounting possible. Load capacity details regarding the different mounting methods are available upon request.

Magnetic shield insulation 15 dB.



A2 Stainless steel

2B Bright, treated

Master data

Item number	6005553
Type	G-GRM 75 50 A2
Description 1	G mesh cable tray Magic
Manufacturer	OBO
Dimension	75x50x3000
Colour	stainless steel
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	3
Unit of quantity	Metre
Weight	79.467 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	4,0695 kg CO2e / 1 Meter


Technical data sheet

G mesh cable tray Magic® 75 A2


Item number: 6005553



Dimensions



Length	3,000 mm
Width	50 mm
Width	1.97 in
Height	75 mm
Height	2.95 in
Dimension A	53 mm
Dimension B	53 mm
Dimension C	38 mm
Dimension H	73 mm



Technical data sheet

G mesh cable tray Magic® 75 A2

Item number: 6005553



Technical data

Connector version	Integrated connector
Mounting system fastening type	Ceiling Wall
Maintain electrical functions	no
Integrated partition	Without
Usable cross-section	22 cm²
Usable cross-section	2200 mm²
Profile shape	G-shaped
Rustproof steel, pickled	yes
Screwless connector	yes
Wide-span version	no
Load test type according to IEC 61537	Type II
Type of connector, cable support system	Click fastening

Loads

Insertable support spacings, min.	1 m
Insertable support spacings, max.	2.5 m