

Technical data sheet

Service outlet with blanking cover and Allen slot, GES R2,
old copper
Item number: 7408874



Service outlet with blanking cover and Allen slot for GES R2 floor socket for direct installation in the MT R2 installation socket in indoor areas.

The cover version can be used as a cable outlet.

When closed, the floor socket can be wet-cleaned.



- Zn** Die-cast zinc
- Cu** Copper-plated

Master data	
Item number	7408874
Description 1	Floor socket
Description 2	blind with Allen key recess
Manufacturer	OBO
Material	Die-cast zinc
Surface	Copper-plated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	58.32 kg
Weight unit	kg/100 pc.


Technical data sheet

Service outlet with blanking cover and Allen slot, GES R2,
old copper

Item number: 7408874



Dimensions



Technical data

Version for	Round
Cable outlet version	No cable outlet
Floor covering protection frame	yes
Floor care	Wet
Suitable for raised floor installation	yes
Suitable for cavity floor installation	yes
Suitable for wet care	yes
Suitable for underfloor ducts	no
With floor covering recess	no
Standard	EN 50085-2-2
Protection rating (IP) when unused	IP66
Protection rating IK code	IK10
Vertical load, large area	to 15,000 N
Vertical load, small area	to 3,000 N
Approvals	VDE
Opening mechanism	Tool