


Technical data sheet

External corner cover, smooth

Item number: 6274790



PVC external corner cover, smooth surface.



Master data	
Item number	6274790
Description 1	Cover
Description 2	external corner, smooth
Manufacturer	OBO
Colour	Pure white; RAL 9010
Material	Polyvinylchloride
Smallest sales unit	1
Unit of quantity	Piece
Weight	9.5 kg
Weight unit	kg/100 pc.


Technical data sheet

External corner cover, smooth

Item number: 6274790



Dimensions



Length	200 mm
Width	76.5 mm
Height	12 mm

Technical data

Application	External corner
Halogen-free	no
Cover mounting type	Internal
Protection rating	IP30
Protective film	yes
Protection rating IK code	IK08
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-15 °C