

Technical data sheet

Plastic trunking cover, smooth

Item number: 6278684



Smooth trunking cover, for closing device installation trunking with 76.5 mm system opening.



PVC Polyvinylchloride

Master data

Item number	6278684
Type	GK-OTGSW
Description 1	Cover
Description 2	smooth
Manufacturer	OBO
Dimension	2000x80
Colour	Jet black; RAL 9005
Material	Polyvinylchloride
Smallest sales unit	2
Unit of quantity	Metre
Weight	27.5 kg
Weight unit	kg/100 m

Dimensions

Length	2,000 mm
Width	76.5 mm
Height	12 mm

Technical data sheet

Plastic trunking cover, smooth

Item number: 6278684



Technical data

Version for	Smooth
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C