

Technical data sheet

Coupling GS-KUP70

Item number: 6277290



Coupling for connecting the trunking bases. This creates the equipotential bonding between the trunking bases.

The scope of delivery of a coupling includes 2 connection plates.



A2 Stainless steel

Master data		
	Item number	6277290
	Description 1	Coupling
	Description 2	universal, f. trunking depth 70
	Manufacturer	OBO
	Dimension	70x120
	Colour	stainless steel
	Material	Stainless steel
	Smallest sales unit	1
	Unit of quantity	Packaging unit
	Weight	6.4 kg
	Weight unit	kg/100 PUs
Dimensions		
	Length	120 mm
	Width	70 mm

Technical data sheet

Coupling GS-KUP70

Item number: 6277290



Technical data

Version for	Universal
Type	coupling
Halogen-free	yes
Trunking depth	70 mm
With equipotential bonding	yes
Protection rating	IP30
Protection rating IK code	IK10
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-25 °C