

Technical data sheet

Hexagonal bolt DIN 933 A4

Item number: 3156022



Hexagonal bolt M6 x 40 mm



A4	Stainless steel
2B	Bright, treated

Master data

Item number	3156022
Type	HHS M6x40 A4
Description 1	Hexagonal screw
Manufacturer	OBO
Dimension	M6x40mm
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	100
Unit of quantity	Piece
Weight	0.923 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0446 kg COe / 1 Piece

Dimensions



Length	40 mm
Dimension d	6 mm
Dimension L	40 mm

Technical data sheet

Hexagonal bolt DIN 933 A4

Item number: 3156022



Technical data

Thread	M6
Thread metric	6
Thread type	Metric
Thread length	40 mm
Head shape	Hexagonal
With flange	no
With nut	no
With washer	no
WAF	10
Screw system	Hexagonal
Self-locking	no
Full thread	yes
Left thread	no