


Technical data sheet

Hexagonal bolt DIN 933 A4

Item number: 3156025



Hexagonal bolt M8 x 25 mm



A4 Stainless steel

2B Bright, treated

Master data

Item number	3156025
Type	HHS M8x25 A4
Description 1	Hexagonal screw
Manufacturer	OBO
Dimension	M8x25mm
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	100
Unit of quantity	Piece
Weight	1.39 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0672 kg COe / 1 Piece


Technical data sheet

Hexagonal bolt DIN 933 A4

Item number: 3156025



Dimensions



Length	25 mm
Dimension d	8 mm
Dimension L	25 mm

Technical data

Thread	M8
Thread metric	8
Thread type	Metric
Thread length	25 mm
Head shape	Hexagonal
With flange	no
With nut	no
With washer	no
WAF	13
Screw system	Hexagonal
Self-locking	no
Full thread	yes
Left thread	no