

Technical data sheet

Flange head screw HT 10

Item number: 3498140



Self-tapping wood screw for fireproof fastening of cable systems for the maintenance of electrical function according to DIN 4102 Part 12 on supporting wooden structures. The flange head shape allows installation without an additional washer.



St	Steel
G	Electrogalvanized

Master data

Item number	3498140
Description 1	Flange head
Description 2	for wood
Manufacturer	OBO
Dimension	10x80
Colour	zinc
Material	Steel
Surface	Electrogalvanized
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	50
Unit of quantity	Piece
Weight	3.1 kg
Weight unit	kg/100 pc.


Technical data sheet

Flange head screw HT 10

Item number: 3498140



Dimensions



Length	80 mm
Dimension D	10 mm
Dimension L	80 mm

Technical data

Hardened	yes
Head diameter	22.5 mm
Head shape	Plate head
Shank diameter	7 mm
Screw system	Torx
Two-compartment	no