

Technical data sheet

Installation unit

Item number: 6288365



Flush-mount unit for the installation of automatic circuit-breakers or FI protection switches in device installation trunking of the series Rapid 80 GK, GS and GA. With 1 hat rail of 3 part units. Series terminals for N and PE on hat rails, completely wired with 6 mm². The cable cross-section is 6 mm². The flush-mount unit is pre-wired and ready for connection. Two type V-Tec M20 cable glands for cable entry are included in the delivery. A maximum of 3 M20 cable glands or 1 M25 cable gland can be mounted on each side.



St	Steel
P	Powder-coated

Master data

Item number	6288365
Type	IKR4RW
Description 1	Flush-mount unit
Description 2	for Rapid 80 GK, GS & GA
Manufacturer	OBO
Dimension	92x84x344
Colour	Pure white; RAL 9010
Material	Steel
Surface	Powder-coated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	85.4 kg
Weight unit	kg/100 pc.

Dimensions



Length	344 mm
Width	84 mm
Height	92 mm

Technical data sheet

Installation unit

Item number: 6288365



Technical data

Extension option	no
Number of units	3
Number of rows	1
Type of cover	With cut-out
DIN rail	yes
Suitable for duct depth	80
Halogen-free	yes
Cable entry	yes
With mounting plate	no
Mounting type	Device installation duct
Transparent lid	yes